

Dr. Packer
B & L Stellaris
Bi-manual
Advance Flow System
August 22, 2007

Phaco			IA	IA Visc. removal	Vit		
	Chop		Flip	IA	BI/COAX	Hi speed	Regular (pneum)
Power %	20 Linear (Waveform not Enabled)		20 linear			Cut rate: 1500 cpm	Cut rate: 600 cpm
Mode	8 pps		Fixed burst Duration: 10 msec Interval: 30 msec			(yaw to turn cutter on/off)	
Duty Cycle %	30		25				
Vac (yaw for max)	350-450		250-325	450 linear	500	150 linear	150 linear
Flow	40 fixed		30 fixed	30 fixed	30	30 fixed	25 fixed
Vacuum Response	1		2				
Bottle ht	140		140	140	140/80	75	50